

NULOG

Innovative Fastener Systems

By Designovations, Inc.

NULOC 1





Fasten by compressing clip ends to open jaws and slid over retaining rings on stem.



Position clip to desired length and release to lock in position

To remove compress clip ends to disengage jaws and slide off stem.

NULOC 2





Fasten by lining up clip with keyway and sliding onto the stem



Next, rotate the clip clockwise to tighten and lock in position

To remove fastener rotate counterclockwise until it stops and slide off stem

Nuloc Fastener Systems are designed to secure a variety of materials including cardboard, plastic or any material where there is access to both the front and back of the item.

Product Applications:

- Sign Fasteners
- Display/POP Fixtures
- Automotive Applications
- Subassembly Processes
- Retractable Awnings
- Medical Devices
- Physical Therapy Equipment
- Furniture
- The Options are Unlimited!

Product Benefits:

- Lock Guarantee Will not vibrate loose
- Adjustable
 - Nuloc 1 1/8" increments
 - **Nuloc 2** Double threaded stem is Infinitely adjustable
- Size
 - Nuloc 1 Standard Size 5/16" Dia. 2" Length
 - Nuloc 2 Standard Sizes 5/16" & 3/16" Dia., up to 3" Length
- Maintenance Free Will not rust
- Color Choice Available in any color
- Reusable Not limited to one application
- Permanency Option Cut clip ends for tamper resistance

